

TIGER-VAC · II 1/2GD EXTERNAL: EX DB H IIB T4 GB -- EX H TB IIIC T135 C DB IP65 -- INTERNAL: EX H IIC T6 GA -- EX H IIIC T50 C DA -- -5 C <= TA <= +37 C -- EN 17348 DT -- LCIE 03 ATEX 6295 X -- IECEx LCI 10.0040X -- ATEX 3RD PARTY -- VARIANT: Z21 CERT (111611B1) M/MFS

Tiger-Vac CD/EUR-50L EX DT (MFS) CAT. 2D Z21



The Tiger-Vac CD/EUR-50L EX DT (MFS) CAT. 2D Z21 (111611B1) is the MFS version of the CD/EUR-50L pharma vacuum platform with Z21 certification. ATEX II 1/2GD 3rd party. Manual Filter Shaker instead of MRP -- simple mechanics that shake the washable static dissipative cloth main filter clean. The True Cyclone Separator on the suction intake significantly increases separation efficiency. 4 kW TEFC, 299 m³/h, 3380 mmH₂O, 74 dB(A). 50 L AISI 304 tank, 63.5 mm intake, ULPA U15 standard. Vertical mounting with CSMT (103 x 69 x 201 cm). Choose MFS if your dust is normally flowing and MFS vibration is sufficient; choose MRP if the dust is sticky or very fine.

APPLICATIONS

- Pharma pilot plants in ISO Class 4 cleanrooms with Z22 dust
- Continuous duty with MRP-efficient filter cleaning
- Vertical mounting where floor space is at a premium
- ATEX housekeeping in pharma production with combined zone marking
- Process production with fine pharma CMR dust requiring effective MRP purge

Technical specifications

ATEX marking	II 1/2GD External: Ex db h IIB T4 Gb -- Ex h tb IIIC T135 C Db IP65 -- Internal: Ex h IIC T6 Ga -- Ex h IIIC T50 C Da -- -5 C <= Ta <= +37 C -- EN 17348 DT -- LCIE 03 ATEX 6295 X -- IECEx LCI 10.0040X -- ATEX 3rd party -- variant: Z21 cert (111611B1) m/MFS
Internal / external zone	20 / 21
Motor type	3-faset TEFC induktion -- eksplosionsbeskyttet (Ex db h IIB T4 Gb / Ex h tb IIIC T135 C Db IP65), 3rd party certified, kontinuerlig drift
Airflow	299 m ³ /h
Vacuum	331 mbar (3380 mmH ₂ O)
Container	50 L
Sound pressure	74 dB(A)
Filter class	H class
Filter type	ULPA U15 (EN 1822-5, 99,999 % MPPS 0,12 micron) standard inkl. -- aerosol leak-testet, OSHA-compliant. HEPA H14 også tilgængelig
Primary filter	Statisk afladende washable klod-hovedfilter i removable filter chamber
Cleaning system	Manual Filter Shaker (MFS) -- mekanisk vibration
Collection system	Detachable container
Material	AISI 304 rustfri stål kabinet (undtagen cart -- som er heavy duty powder coated -- AISI 304 cart som tilvalg til pharma)
IP class	IP65
Power	4.0 kW
Current	8.2 A
Voltage	400 V / 50 Hz / 3~
Inlet	Diameter 63.5 mm
Dimensions (L x W x H)	1030 x 690 x 2010 mm
Weight	60 kg

Questions and answers

What is the difference between the three MRP ULPA certifications (Z22 / Z21 / Z1-2-21-22)?

Drive specs are identical (4 kW, 299 m³/h, 3380 mmH₂O, 50 L tank, 60 kg). The difference is the underlying ATEX certification, which determines in which zones the unit may formally be used: Z22 (111625B1) is Zone 22 dust only; Z21 (111629B1) is Zone 21 dust; Z1-2-21-22 (111633B1) is combined -- Zone 1 and 2 gas + Zone 21 and 22 dust. Choose the variant based on the zone classification at your site -- contact us for advice if in doubt.

What is CSMT?

CSMT = Carriage with Suspended Motor Top. A construction where the motor hangs from a common frame design above the tank platform itself -- giving a small footprint and easy mobility even at 60 kg weight and 210 cm height. CSMT is industry standard at Tiger-Vac for high-flow vertically mounted ATEX models.

What is the advantage of MRP over MFS?

MFS (Manual Filter Shaker) shakes the filter with vibration -- simple mechanics. MRP (Manual Reverse Purge) uses reverse purge through the cartridge, breaking the filter cake loose effectively -- better for sticky, damp or very fine dust. The CD/EUR-50L MRP-ULPA version is specifically designed for pharma powder and CMR substances where MFS vibration is not sufficient.

Can it pick up liquids?

No. The CD/EUR-50L MRP ULPA is Dry Recovery Only per EN 17348 DT. For wet/dry recovery in combined zones see the CD-3 EX (W&D;) or CD-63L EX (W&D;) series.

Contact and advisory

PARTICULAIR

Particulair

Højtoften 12

2690 Karlslunde, Denmark

CVR: 34129894

Phone: (+45) 70 23 12 03

E-mail: sales@particulair.com

Web: particulair.eu

Product page: particulair.eu/ex-vac/en/atex-combi/cd-eur-50l-ex-dt-mfs-cat-2d-z21/

SMARTER THINKING • BETTER WORKING

This datasheet is generated deterministically from Particulair product data. Prices and availability provided on request. All specifications subject to change without notice.