

## ACCESSORIES

# CONNECT 226

Screw-on soft sleeve for SUPERFLEX 372 - chemically resistant, quick, reusable



CONNECT 226 is a screw-on based soft sleeve specifically developed for the SUPERFLEX 372 hose. The construction is chemically resistant and supplied in black. The screw-on mechanism allows quick mounting and disassembly without special tools - the sleeve can be reused multiple times without losing seal integrity. 9 dimensions cover SUPERFLEX 372's standard range from ID 25 mm to 76 mm. Typically used in process installations where periodic hose replacement is necessary - e.g. during chemical cleaning, sterilisation or configuration changes.

**Temp:** -20.0 °C to 70.0 °C

## Technical specifications

<b>Colour</b>	black
<b>Wall construction</b>	Screw-on soft sleeve - chemically resistant, reusable
<b>Temperature range</b>	-20.0 °C – 70.0 °C
<b>Short-term peak</b>	80.0 °C
<b>Cut to length</b>	No
<b>Manufacturer SKU</b>	2260000

### Standards and compliance

REACH, RoHS

## Dimensions and ordering

The hose is supplied in 9 standard sizes from inner Ø 25.0 mm to 76.0 mm. Each size has its own article number. Standard roll length is typically 10 m, and the hose can be cut to length.

Inner Ø [mm]	Outer Ø [mm]	Max len. [m]	Weight [kg/m]	Article no.
25	25	100	0.05	22600250000
32	32	100	0.06	22600320000
38	38	100	0.07	22600380000
41	41	100	0.07	22600410000
44	44	100	0.08	22600440000
51	51	100	0.09	22600510000
63	63	100	0.13	22600630000
70	70	100	0.15	22600700000
76	76	100	0.17	22600760000

The table shows the hose's internal diameter (ID), receiving nozzle diameter (OD), and sleeve total length. Weight column is per piece.

## Other Particulair microsities

---

We build specialised microsities for critical industries. Each site provides in-depth product data, documentation and expert guidance for the domain it covers.

<a href="https://particulair.eu/ex-vac">particulair.eu/ex-vac</a>	ATEX and ACD vacuum cleaners for explosion hazard zones
<a href="https://particulair.eu/vace">particulair.eu/vace</a>	Nozzles and accessories for critical environments
<a href="https://particulair.eu/life-science">particulair.eu/life-science</a>	Vacuums for pharma and cleanroom
<a href="https://particulair.eu/hardo">particulair.eu/hardo</a>	Explosion-protected electrical Ex-equipment

## Contact and advisory

---

### Particulair

Højtoften 12  
2690 Karlslunde, Denmark  
CVR: 34129894

Phone: (+45) 70 23 12 03  
E-mail: [sales@particulair.com](mailto:sales@particulair.com)  
Web: [particulair.eu](https://particulair.eu)

**Product page:** [particulair.eu/flexcore/en/accessories/connect-226/](https://particulair.eu/flexcore/en/accessories/connect-226/)

---

### SMARTER THINKING • BETTER WORKING

This datasheet is generated automatically from Particulair product data. All specifications are taken from the manufacturer's factsheet and are subject to change without notice. Prices and availability provided on request.